

Posts for Stands / Caps for Hollow Posts

Posts for Stands With Scale / Length Configurable with Scale

■ **Features:** Can be used in combination with Device Stands, Stand-Up Brackets and Strut Clamps.

■ **Posts for Stands**

Type		Material	Hardness	Surface Treatment
Solid	Hollow			
STN	STA	EN 1.1191 Equiv. 58HRC-Case Induction Hardened (Depth 1.0 ~ 1.5)		Electroless Nickel Plating
STNM	STAM			
MSTNM	MSTAM	EN 1.1191 Equiv.		Electroless Nickel Plating
GSTNM	GSTAM	EN 1.1191 Equiv.		Black Oxide
STNUG	SMSTAM	EN 1.4301 Equiv.		-

⚠ Surface treatment may not be applied to ends and grooves of STNM, STAM, MSTNM, MSTAM, GSTNM, GSTAM.

Type	Part Number	Dg6	L		(D1)	l	h	(d)	
			1mm Increment	mm					
Solid STN STNM MSTNM GSTNM STNUG	Hollow STA STAM MSTAM GSTAM SMSTAM	6	-0.004 -0.012	30~150	4.5	12	4	-	
		8	-0.005	30~200	6.5	15			
		10	-0.014	35~250	8.5	18			
			12	-0.006	35~300	10	18	5	6.0
			15	-0.017	40~350	13	20		
			20	-0.007	45~400	17	25	6	10.0
			25	-0.007	50~450	22	30		
			30	-0.020	60~450	27	30	8	11.7
			35	-0.009	70~500	32	40		
			40	-0.025	80~500	37	40	10	15.2
	50	-0.025	100~600	46	50				

⚠ Hollow Posts are available from D10. STN is applicable from D8.

Ordering Example: Part Number - L
STNUG12 - 250

Alterations

Alteration	Code	Spec.
No Groove	MN	Alteration to No Set Screw Groove. (Ordering Code) MN
One End Tapped	MTC	Tapped at one end. (Ordering Code) MTC8

⚠ Applicable to Solid Type only.
⚠ Not applicable to D=6.

D	L	Unit Price									
		Solid					Hollow				
		STN	STNM	MSTNM	GSTNM	STNUG	STA	STAM	MSTAM	GSTAM	SMSTAM
6	30~100	-	-	-	-	-	-	-	-	-	-
	101~150	-	-	-	-	-	-	-	-	-	-
8	30~100	-	-	-	-	-	-	-	-	-	-
	101~200	-	-	-	-	-	-	-	-	-	-
10	35~150	-	-	-	-	-	-	-	-	-	-
	151~250	-	-	-	-	-	-	-	-	-	-
12	35~150	-	-	-	-	-	-	-	-	-	-
	151~300	-	-	-	-	-	-	-	-	-	-
15	40~200	-	-	-	-	-	-	-	-	-	-
	201~350	-	-	-	-	-	-	-	-	-	-
20	45~200	-	-	-	-	-	-	-	-	-	-
	201~400	-	-	-	-	-	-	-	-	-	-
25	50~200	-	-	-	-	-	-	-	-	-	-
	201~450	-	-	-	-	-	-	-	-	-	-
30	60~200	-	-	-	-	-	-	-	-	-	-
	201~450	-	-	-	-	-	-	-	-	-	-
35	70~300	-	-	-	-	-	-	-	-	-	-
	301~500	-	-	-	-	-	-	-	-	-	-
40	80~300	-	-	-	-	-	-	-	-	-	-
	301~500	-	-	-	-	-	-	-	-	-	-
50	100~300	-	-	-	-	-	-	-	-	-	-
	301~600	-	-	-	-	-	-	-	-	-	-

■ **Features:** Caps can be mounted on the end face of Hollow Posts on P2145~P2152.

■ **Caps for Hollow Posts**

Material: Natural Rubber (NR70)

Part Number	Type	No.	D	d	d1	T	Unit Price	Volume Discount Rate
10	CAP	9	6.2	3	8	1	1 ~ 19 pcs(s).	20 ~ 50 pcs.
12		11	3					
15		14	6					
20		18	10					
25		23	15					
30		28	20	10				
35		33	25					
40		38	30					
50		48	40					

⚠ For orders larger than indicated quantity, please check with WOS.

Ordering Example: Part Number - L
CAP25

■ **Features:** Easy to adjust positions of cameras and sensors during setup changes. Hollow Type is capable of storing wiring.

■ **With Scale**

Type		Material
Solid	Hollow	EN 1.4301 Equiv.
GSSTN	GSSTA	

⚠ If wiped with volatile oil, the prints may fade.
⚠ The scale graduations are represented in centimeters.
⚠ Use the scale as a reference.
* Scale indicates up to (L-20)/10.

Part Number	Type	Dg6	L Selection	(d)	Unit Price										
					GSSTN					GSSTA					
					L100	L150	L200	L250	L300	L100	L150	L200	L250	L300	
GSSTN GSSTA	10	-0.013 -0.035	100 150 200	8											
	12	-0.016	100 150 200 250 300	10											
	15	-0.043	100 150 200 250 300	12.6											
	20	-0.020 -0.053	100 150 200 250 300	16											
	25		200 250 300	-											

Ordering Example: Part Number - L
GSSTN15 - 200
GSSTA20 - 300

■ **Length Configurable with Scale**

Type		Material
Solid	Hollow	EN 1.4301 Equiv.
FGSTN	FGSTA	

⚠ If wiped with volatile oil, the prints may fade.
⚠ Scale is without numbers.
⚠ Use the scale as a reference.

Part Number	Type	Dg6	L Selection	(d)	Unit Price					
					FGSTN			FGSTA		
					Min. L ~ 200	201~400	401~450	Min. L ~ 200	201~400	401~450
FGSTN FGSTA	10	-0.013 -0.035	35~450	8						
	12	-0.016	35~450	10						
	15	-0.043	40~450	12.6						
	20	-0.020 -0.053	45~450	16						
	25		50~450	20						

Ordering Example: Part Number - L
FGSTN10 - 100
FGSTA20 - 200

Example