Captured Washer Phillips Pan Head Screws / Phillips Pan Head Screws
Stainless Steel (Available in Box)



■Phillips Pan Head Screws with Captured Washer

Type	Part Number	Material
BOX-SCBJ	Screw	EN 1.4301 Equiv.
	Spring Washer	EN 1.4301 Equiv.
	Flat Washer	



MxP (Coarse)	A	E	C	D	(a)	Phillips No.
2 x0.4	3.5	1.3	4	6	2.1	1
2.5x0.45	4.5	1.7	4.8	7.5	2.7	1
2.6x0.45	4.5	1.7	4.8	7.5	2.7	1
3 x0.5	5.5	2	5.5	8	3	2
4 x0.7	7	2.6	7	10	4.4	2
5 x0.8	9	3.3	8.5	12	5.4	2
6 x1.0	10.5	3.9	11.5	13	6.9	3

(a) is the max length (reference) between head surface and the complete thread.
Can be ordered as a separate item. P.227



■Phillips Pan Head Screws

Type	Material
BOX-NKJ	EN 1.4301 Equiv.



MxP (Coarse)	A	E	Phillips No.
2 x0.4	3.5	1.3	1
2.5x0.45	4.5	1.7	1
2.6x0.45	4.5	1.7	1
3 x0.5	5.5	2	2
4 x0.7	7	2.6	2
5 x0.8	9	3.3	2
6 x1.0	10.5	3.9	3

Can be ordered as a separate item. P.226
Please specify in box quantity when ordering.
One box is shipped for an order of 1.

Ordering Example — Part Number: BOX-SCBJ5-10, BOX-NKJ5-10

■Box package is cost-saving for in-house stock or when large quantities are needed.

Part Number		Unit Price 1 to 10 boxes		Pcs./ Box
Type	M-L	Price per pkg.	1 Box	
BOX-SCBJ (Stainless Steel)	2- 4, 5, 6, 8			500 pcs./box
	2.5- 4, 5, 6, 8, 10			
	2.6- 4, 5, 6, 8, 10			
	3- 5, 6, 8, 10			
	4- 5, 6, 8, 10			
	5- 8, 10, 12, 15			
	6-10, 12, 15			200 pcs./box

For orders larger than indicated quantity, please check with WOS.

Part Number		Unit Price 1 to 10 boxes		Pcs./ Box
Type	M-L	Price per pkg.	1 Box	
BOX-NKJ (Stainless Steel)	2- 3, 4, 5, 6, 8			2,000 pcs./box
	2.5- 3, 4, 5, 6, 8, 10			
	2.6- 3, 4, 5, 6, 8, 10			
	3- 5, 6, 8, 10			
	4- 5, 6, 8, 10			1,000 pcs./box
	5- 8, 10, 12, 15			500 pcs./box
	6-10, 12, 15			300 pcs./box

For orders larger than indicated quantity, please check with WOS.

Phillips Pan Head Screws / Precision Machine Screws
Single Item Sale — Pkg. Sale

■Phillips Pan Head Screws



Type	Material	Surface Treatment
BKJ	JIS-SWCH Equiv.	Trivalent Chromate
NKJ	EN 1.4301 Equiv.	-



MxP (Coarse)	A	E	Phillips No.
2x0.4	3.5	1.3	1
2.5x0.45	4.5	1.7	1
2.6x0.45	4.5	1.7	1
3x0.5	5.5	2	2
4x0.7	7	2.6	2
5x0.8	9	3.3	2
6x1.0	10.5	3.9	3

■BKJ (Trivalent Chromate)

Part Number		Unit Price	Volume Discount Rate		
Type	M - L	1 ~ 29 pc(s).	30 ~ 99 pcs.	100 ~ 299 pcs.	300 ~ 500 pcs.
BKJ	2 - 2, 3, 4, 5, 6, 8, 10				
	3 - 3, 4, 5, 6, 8, 10, 12				
	4 - 4, 5, 6, 8, 10, 12, 15				
	5 - 6, 8, 10, 12, 15				
	6 - 10, 12, 15, 20				

■NKJ (Stainless Steel)

Part Number		Unit Price	Volume Discount Rate		
Type	M - L	1 ~ 29 pc(s).	30 ~ 99 pcs.	100 ~ 149 pcs.	150 ~ 500 pcs.
NKJ	2 - 2, 3, 4, 5, 6, 8, 10				
	2.5 - 3, 4, 5, 6, 8, 10				
	2.6 - 3, 4, 5, 6, 8, 10				
	3 - 3, 4, 5, 6, 8, 10, 12, 15				
	4 - 4, 5, 6, 8, 10, 12, 15				
	5 - 6, 8, 10, 12, 15, 20				
	6 - 10, 12, 15, 20				

Ordering Example — Part Number: NKJ3-6

■Precision Machine Screws (Package)



PACK-MIB
PACK-SMIB
(Stainless Steel)



Type	Material	Surface Treatment
PACK-MIB	JIS-SWCH16A	Trivalent Black
PACK-SMIB	EN 1.4301 Equiv.	-

No. 0, Type 1 Pan Head Screw

Part Number								MxP	D	E	r (Max.)	(e) (Max.)	Qty. / Pack	Unit Price	Volume Discount Rate
Type	M	L												1 ~ 2 pkg(s).	3~10 pkgs.
PACK-MIB PACK-SMIB	1.2	2	3	4	5	*6	*8	1.2x0.25	1.8	0.5	0.05	0.4	50 pcs./pkg.		
	1.4	2	3	4	5	6	8	1.4x0.3	2			0.5			
	1.6	2	3	4	5	6	8	1.6x0.35	2.4	0.55		0.6			
	1.7	2	3	4	5	6	8	1.7x0.35	2.5	0.5					
	2.0	2	3	4	5	6	8	2.0x0.4	3	0.6					

The sizes marked with * are available for PACK-SMIB only.
For orders larger than indicated quantity, please check with WOS.

Ordering Example — Part Number: PACK-MIB1.6-5
When placing an order, please specify number of packages. 1 package will be delivered for an order for 1.

Phillips Pan Head Screws with Captured Washer

Single Item Sale

■Phillips Pan Head Screws with Captured Washer
SW+JIS W Captured



RoHS

NSET
SCBJ



NSET

Screw	MMaterial: JIS-SWCH Equiv.
Washers	Spring Washer JIS B 1251 Flat Washer JIS B 1256
SSurface Treatment	Trivalent Chromate

SCBJ

Screw	MMaterial: EN 1.4301 Equiv.
Washers	Spring Washer JIS B 1251 Flat Washer JIS B 1256

MxP	A	E	C (Max.)	D	(a)	Phillips No.
2 x0.4	3.5	1.3	4.0	6.0	2.1	1
2.5x0.45	4.5	1.7	4.8	6.5	2.7	1
2.6x0.45	4.5	1.7	4.8	7.5	2.7	1
3 x0.5	5.5	2.0	5.5	8.0	3.0	2
4 x0.7	7.0	2.6	7.0	10.0	4.4	2
5 x0.8	9.0	3.3	8.5	12.0	5.4	2
6 x1.0	10.5	3.9	11.5	13.0	6.9	3

Part Number		NSET		SCBJ			
		Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate		
Type	M-L	1 ~ 99 pc(s).	100 ~ 500 pcs.	1 ~ 29 pc(s).	30 ~ 99 pcs.	100 ~ 149 pcs.	150 ~ 500 pcs.
NSET SCBJ	2 - 4						
	5						
	6						
	8						
	2.5 - 4	-	-				
	5	-	-				
	6	-	-				
	8	-	-				
	10	-	-				
	2.6 - 4			-	-	-	-
	5			-	-	-	-
	6			-	-	-	-
	8			-	-	-	-
	10			-	-	-	-
	3 - 5			-	-	-	-
	6						
	8						
	10						
	12						
	14			-	-	-	-
	15			-	-	-	-
	16			-	-	-	-
	20			-	-	-	-
	25			-	-	-	-
	30			-	-	-	-
	35			-	-	-	-
	40			-	-	-	-
	45			-	-	-	-
	50			-	-	-	-
	4 - 5						
	6						
	8						
	10						
	12						
	14			-	-	-	-
	16						
	20			-	-	-	-
	25			-	-	-	-
	30			-	-	-	-
	35			-	-	-	-
	40			-	-	-	-
	45			-	-	-	-
	50			-	-	-	-
	5 - 8						
	10						
	12						
	14			-	-	-	-
	16						
	20			-	-	-	-
	25			-	-	-	-
	30			-	-	-	-
	35			-	-	-	-
	40			-	-	-	-
	45			-	-	-	-
	50			-	-	-	-
	6 - 10						
	12						
	14			-	-	-	-
	16						
	20						
	25			-	-	-	-
	30			-	-	-	-
	35			-	-	-	-
	40			-	-	-	-
	45			-	-	-	-
	50			-	-	-	-

■Phillips Pan Head Screws with Captured Washer
SW+JIS Compact W Captured



RoHS

PSET
PSETS



PSET

Screw	MMaterial: JIS-SWCH Equiv.
Washers	Spring Washer JIS B 1251 Flat Washer JIS B 1256
SSurface Treatment	Trivalent Chromate

PSETS

Screw	MMaterial: EN 1.4301 Equiv.
Washers	Spring Washer JIS B 1251 Flat Washer JIS B 1256

MxP	A	E	C (Max.)	D	(a)	Phillips No.
3x0.5	5.5	2.0	5.5	6.0	3.0	2
4x0.7	7.0	2.6	7.0	8.0	4.4	2
5x0.8	9.0	3.3	8.5	10.0	5.4	2
6x1.0	10.5	3.9	11.5	11.5	6.9	3

Part Number		PSET				PSETS			
		Unit Price	Volume Discount Rate			Unit Price	Volume Discount Rate		
Type	M-L	1 ~ 29 pc(s).	30 ~ 99 pcs.	100 ~ 149 pcs.	150 ~ 500 pcs.	1 ~ 29 pc(s).	30 ~ 99 pcs.	100 ~ 149 pcs.	150 ~ 500 pcs.
PSET PSETS	3 - 6								
	8								
	10								
	12								
	4 - 6								
	8								
	10								
	12								
	15								
	5 - 8								
	10								
	12								
	15								
	6 - 10								
	12								
	15								
	20								

Ordering Example — Part Number: SCBJ6-10, PSET3-6

■Phillips Pan Head Screws with Captured Washer
SW Captured



RoHS

WSET
WSETS



WSET

Screw	MMaterial: JIS-SWCH Equiv.
Washers	Spring Washer JIS B 1251 Flat Washer JIS B 1256
SSurface Treatment	Trivalent Chromate

WSETS

Screw	MMaterial: EN 1.4301 Equiv.
Washers	Spring Washer JIS B 1251 Flat Washer JIS B 1256

MxP	A	E	C (Max.)	(a)	Phillips No.
3x0.5	5.5	2.0	5.5	2.4	2
4x0.7	7.0	2.6	7.0	3.5	2
5x0.8	9.0	3.3	8.5	4.3	2
6x1.0	10.5	3.9	11.5	5.1	3

Part Number		WSET				WSETS			
		Unit Price	Volume Discount Rate			Unit Price	Volume Discount Rate		
Type	M-L	1 ~ 29 pc(s).	30 ~ 99 pcs.	100 ~ 199 pcs.	200 ~ 500 pcs.	1 ~ 29 pc(s).	30 ~ 99 pcs.	100 ~ 199 pcs.	200 ~ 500 pcs.
WSET WSETS	3 - 6								
	8								
	10								
	12								
	4 - 8								
	10								
	12								
	15								
	5 - 8								
	10								
	12								
	15								
	6 - 10								
	12								
	15								
	20								

■Phillips Hex Head Screws with Captured Washer

BSET
SBSET (Stainless Steel)



RoHS



BSET

Screw	MMaterial: Structural Alloy Steel Screw: JIS 0209 (6g)
Washers	Spring Washer JIS B1251 Flat Washer JIS B1256
SSurface Treatment	Trivalent Chromate

SBSET

Screw	MMaterial: EN 1.4301 Equiv. *Strength Class A2-50 Equiv. Screw: JIS 0209 (6g)
Washers	Spring Washer JIS B1251 Flat Washer JIS B1256
SSurface Treatment	Barrel, Passivated

MxP	A	E	C	D	(a)
4x0.7	7	2.8	7.0	10	4.4
5x0.8	8	3.5	8.5	12	5.2
6x1.0	10	4.0	11.5	13	6.3
8x1.25	13	5.5	14.5	18	8.4

(a) is the max length (reference) between head surface and the complete thread.

Part Number		BSET		SBSET	
		Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
Type	M-L	1 ~ 99 pc(s).	100 ~ 500 pcs.	1 ~ 99 pc(s).	100 ~ 500 pcs.
BSET SBSET	4- 8				
	10				
	12				
	14				
	16				
	20				
	25			-	-
	30			-	-
	35			-	-
	40			-	-
	45			-	-
	50			-	-
BSET SBSET	5-10				
	12				
	14				
	16				
	20				
	25				
	30				
	35			-	-
	40			-	-
	45			-	-
	50			-	-
BSET SBSET	6-10				
	12				
	14				
	16				

Part Number		BSET		SBSET	
		Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
Type	M-L	1 ~ 99 pc(s).	100 ~ 500 pcs.	1 ~ 99 pc(s).	100 ~ 500 pcs.
BSET	6-20				
SBSET	25				
	30				
	35			-	-
	40			-	-
	45			-	-
	50			-	-
	55			-	-
	60			-	-
	65			-	-
	70			-	-
	75			-	-
BSET	8-12				
SBSET	14				
	16				
	20				
	25				
	30				
	35			-	-
	40			-	-
	45			-	-
	50			-	-
	55			-	-
	60			-	-
	65			-	-
	70			-	-
	75			-	-

Ordering Example — Part Number: WSET5-10, BSET4-8

Phillips Flat Head Screws
Stainless Steel (Available in Box)



RoHS

Type	Material
BOX-SFBJ	EN 1.4301 Equiv.



MxP (Coarse)	A	E	Phillips No.
2 x0.4	4	1.2	1
2.5x0.45	5	1.45	1
2.6x0.45	5.2	1.5	1
3 x0.5	6	1.75	2
4 x0.7	8	2.3	2
5 x0.8	10	2.8	2
6 x1.0	12	3.4	3

Can be ordered as a separate item. P.230

Please specify in box quantity when ordering.
One box is shipped for an order of 1.

Ordering Example — Part Number: BOX-SFBJ5-10

■Box package is cost-saving for in-house stock or when large quantities are needed.

Part Number		Unit Price 1 to 10 boxes		Pcs./ Box
Type	M-L	Price per pkg.	1 Box	
BOX-SFBJ (Stainless Steel)	2- 3			2,000 pcs./box
	4			
	5			
	6			
	8			
	2.5- 3			
	4			
	5			
	6			
	8			
	10			
	2.6- 3			
	4			
	5			
	6			
	8			
	10			
	3- 5			
	6			
	8			
	10			
	4- 5			1,000 pcs./box
	6			
	8			
	10			
	5- 8			500 pcs./box
	10			
	12			
	15			
	6-10			300 pcs./box
	12			
	15			

Phillips Flat Head Screws / Phillips Low Flat Head Screws
Single Item Sale

■Phillips Flat Head Screws



RoHS

Type	Material	Surface Treatment
BFBJ	JIS-SWCH Equiv.	Trivalent Chromate
SFBJ	EN 1.4301 Equiv.	-



MxP (Coarse)	A	E	Phillips No.
2x0.4	4	1.2	1
2.5x0.45	5	1.45	1
2.6x0.45	5.2	1.5	1
3x0.5	6	1.75	2
4x0.7	8	2.3	2
5x0.8	10	2.8	2
6x1.0	12	3.4	3

■BFBJ (Trivalent Chromate)

Part Number		Unit Price	Volume Discount Rate		
Type	M - L	1 ~ 29 pc(s).	30 ~ 99 pcs.	100 ~ 299 pcs.	300 ~ 500 pcs.
BFBJ	2 - 3				
	4				
	5				
	6				
	8				
	3 - 4				
	5				
	6				
	8				
	10				
	12				
	4 - 5				
	6				
	8				
	10				
	12				
	15				
	5 - 6				
	8				
	10				
	12				
	15				
	20				
	6 - 8				
	10				
	12				
	15				
	20				

Ordering Example — Part Number: SFBJ4-10

■SFBJ (Stainless Steel)

Part Number		Unit Price	Volume Discount Rate		
Type	M - L	1 ~ 29 pc(s).	30 ~ 99 pcs.	100 ~ 149 pcs.	150~ 500 pcs.
SFBJ	2 - 3				
	4				
	5				
	6				
	8				
	10				
	2.5 - 3				
	4				
	5				
	6				
	8				
	10				
	2.6 - 3				
	4				
	5				
	6				
	8				
	10				
	3 - 4				
	5				
	6				
	8				
	10				
	12				
	4 - 5				
	6				
	8				
	10				
	12				
	15				
	5 - 6				
	8				
	10				
	12				
	15				
	20				
	6 - 8				
	10				
	12				
	15				
	20				

■Phillips Low Flat Head Screws



RoHS

Type	Material	Surface Treatment
TSARA	JIS-SWCH Equiv.	Trivalent Chromate
TSARAS	EN 1.4301 Equiv.	-



MxP (Coarse)	A	E	Phillips No.
3x0.5	5	1.3	1
4x0.7	6	1.4	2
5x0.8	8	1.9	2
6x1.0	10	2.4	2

■TSARA (Trivalent Chromate)

Part Number		Unit Price	Volume Discount Rate		
Type	M - L	1 ~ 19 pc(s).	20 ~ 99 pcs.	100 ~ 199 pcs.	200 ~ 500 pcs.
TSARA	3 - 5				
	6				
	8				
	10				
	12				
	15				
	4 - 6				
	8				
	10				
	12				
	15				
	20				
	25				
	30				
	5 - 8				
	10				
	12				
	15				
	20				
	25				
	30				
	6 - 10				
	12				
	15				
	20				
	25				
	30				

Ordering Example — Part Number: TSARA5-10

■TSARAS (Stainless Steel)

Part Number		Unit Price	Volume Discount Rate		
Type	M - L	1 ~ 19 pc(s).	20 ~ 99 pcs.	100 ~ 199 pcs.	200 ~ 500 pcs.
TSARAS	3 - 5		-	-	-
	6				
	8				
	10				
	12				
	15				
	4 - 6				
	8				
	10				
	12				
	15				
	20				
	25				
	30				
	5 - 8				
	10				
	12				
	15				
	20				
	25				
	30				
	6 - 10				
	12				
	15				
	20				
	25				
	30				

Phillips Binding Head Screws

■Phillips Round Flat Head Screws



RoHS

Type	Material	Surface Treatment
MSARA	JIS-SWCH Equiv.	Trivalent Chromate
MSARAS	EN 1.4301 Equiv.	-



MxP (Coarse)	A	(f)	E	Phillips No.
3x0.5	6	0.7	1.75	2
4x0.7	8	0.9	2.3	2
5x0.8	10	1.2	2.8	2
6x1.0	12	1.4	3.4	3

■MSARA (Trivalent Chromate)

Part Number Type	M - L	Unit Price 1 ~ 29 pc(s).	Volume Discount Rate 30 ~ 99 pcs.	100 ~ 299 pcs.	300 ~ 500 pcs.
MSARA	3 - 5				
	6				
	8				
	10				
	12				
	4 - 6				
	8				
	10				
	12				
	15				
	5 - 8				
	10				
	12				
	15				
	20				
	6 - 10				
	12				
	15				
	20				

■MSARAS (Stainless Steel)

Part Number Type	M - L	Unit Price 1 ~ 29 pc(s).	Volume Discount Rate 30 ~ 99 pcs.	100 ~ 299 pcs.	300 ~ 500 pcs.
MSARAS	3 - 5	-	-	-	-
	6				
	8				
	10				
	12				
	4 - 6				
	8				
	10				
	12				
	15				
	5 - 8				
	10				
	12				
	15				
	20				
	6 - 10				
	12				
	15				
	20				

Ordering Example — Part Number: MSARAS4-8

■Ornamental Screws Washers for Ornamental Screw



RoHS

VIS (Brass)
VISS (Stainless Steel)



VISZ (Brass)
VIZS (Stainless Steel)



Type	Material	Surface Treatment
VIS	EN CW508L Equiv.	Nickel Plating
VISS	EN 1.4301 Equiv.	-
VISZ	EN CW508L Equiv.	Nickel Plating
VIZS	EN 1.4305 Equiv.	-

M (Coarse)	P (Pitch)	D
3	0.5	6
4	0.7	8
5	0.8	10
6	1.0	12

■Ornamental Screws

Part Number Type	M-L	Unit Price 1 ~ 99 pc(s).	Volume Discount Rate 100 ~ 500 pcs.
VIS (Brass)	3-10		
	15		
	20		
	25		
	30		
	35		
	40		
	45		
	50		
	4-10		
	15		
	20		
	30		
	35		
	40		
	45		
	50		

Part Number Type	M-L	Unit Price 1 ~ 99 pc(s).	Volume Discount Rate 100 ~ 500 pcs.
VIS (Brass)	5-10		
	15		
	20		
	25		
	30		
	35		
	40		
	45		
	50		
	6-10		
	15		
	20		
	25		
	30		
	35		
	40		
	45		
	50		

Part Number Type	M-L	Unit Price 1 ~ 99 pc(s).	Volume Discount Rate 100 ~ 500 pcs.
VISS (Stainless Steel)	3-10		
	15		
	20		
	25		
	30		
	4-10		
	15		
	20		
	25		
	30		
	5-10		
	15		
	20		
	25		
	30		
	6-10		
	15		
	20		
	25		
	30		

Ordering Example — Part Number: VIS5-30, VISZ4

■Washers for Ornamental Screw

Part Number Type	d	D	t	Unit Price * Less than	Volume Discount Rate * or More	* Quantity
VISZ (Brass)	3	10	2			2500
	4	12	2.5			1400
	5	14	3			800
	6	16	3.5			500
VIZS (Stainless Steel)	3	10	2			500
	4	12	2.5			400
	5	14	3			300
	6	16	3.5			200



RoHS

Type	Material	Surface Treatment
BDJ	JIS-SWCH Equiv.	Trivalent Chromate
BDJS	EN 1.4301 Equiv.	-



MxP (Coarse)	A	E	Phillips No.
3x0.5	6.3	1.9	2
4x0.7	8.3	2.5	2
5x0.8	10.3	3.1	2
6x1.0	12.4	3.7	3

■BDJ (Trivalent Chromate)

Part Number Type	M - L	Unit Price 1 ~ 9 pc(s).	Volume Discount Rate 10 ~ 29 pcs.	30 ~ 49 pcs.	50 ~ 500 pcs.
BDJ	3 - 5				
	6				
	8				
	10				
	12				
	15	-	-	-	-
	20				
	4 - 6				
	8				
	10				
	12				
	15	-	-	-	-
	20				
	25	-	-	-	-
	30				
	5 - 8				
	10				
	12				
	15				
	20	-	-	-	-
	25				
	30				
	6 - 10				
	12				
	15				
	20	-	-	-	-
	25				
	30				

■BDJS (Stainless Steel)

Part Number Type	M - L	Unit Price 1 ~ 9 pc(s).	Volume Discount Rate 10 ~ 29 pcs.	30 ~ 49 pcs.	50 ~ 500 pcs.
BDJS	3 - 5				
	6				
	8				
	10				
	12				
	15				
	20				
	4 - 6				
	8				
	10				
	12				
	15				
	20				
	25				
	30				
	5 - 8				
	10				
	12				
	15				
	20				
	25				
	30				
	6 - 10				
	12				
	15				
	20				
	25				
	30				

Ordering Example — Part Number: BDJ5-10

Phillips Truss Machine Screws
Stainless Steel (Available in Box)



Type	Material
BOX-TRSS	EN 1.4301 Equiv.



MxP (Coarse)	A	E	Phillips No.
2 x0.4	4.5	1.2	1
2.5x0.45	5.7	1.5	1
2.6x0.45	5.9	1.6	1
3 x0.5	6.9	1.9	1
4 x0.7	9.4	2.5	2
5 x0.8	11.8	3.1	2
6 x1.0	14	3.7	3

Can be ordered as a separate item. P.234

Please specify in box quantity when ordering.
One box is shipped for an order of 1.

Ordering Example — Part Number: BOX-TRSS5-10

■Box package is cost-saving for in-house stock or when large quantities are needed.

Part Number		Unit Price 1 to 10 boxes		Pcs./ Box
Type	M-L	Price per pkg.	1 Box	
BOX-TRSS (Stainless Steel)	2- 3			2,000 pcs./box
	4			
	5			
	6			
	8			
	2.5- 3			
	4			
	5			
	6			
	8			
	10			
	2.6- 3			
	4			
	5			
	6			
	8			
	10			
	3- 5			
	6			
	8			
	10			
	4- 5			1,000 pcs./box
	6			
	8			
	10			
	5- 8			500 pcs./box
	10			
	12			
	15			
	20			
	6-10			300 pcs./box
	12			
	15			
	20			

Phillips Truss Machine Screws
Stainless Steel (Available in Single item)



Type	Material	Surface Treatment
BTRSS	JIS-SWCH Equiv.	Trivalent Chromate
TRSS	EN 1.4301 Equiv.	-



MxP (Coarse)	A	E	Phillips No.
2x0.4	4.5	1.2	1
2.5x0.45	5.7	1.5	1
2.6x0.45	5.9	1.6	1
3x0.5	6.9	1.9	1
4x0.7	9.4	2.5	2
5x0.8	11.8	3.1	2
6x1.0	14	3.7	3

■BTRSS (Trivalent Chromate)

Part Number		Unit Price	Volume Discount Rate		
Type	M - L	1 ~ 29 pc(s).	30 ~ 99 pcs.	100 ~ 249 pcs.	250 ~ 500 pcs.
BTRSS	3 - 4				
	5				
	6				
	8				
	10				
	12				
	4 - 4				
	5				
	6				
	8				
	10				
	12				
	15				
	5 - 5				
	6				
	8				
	10				
	12				
	15				
	20				
	6 - 8				
	10				
	12				
	15				
	20				

Ordering Example — Part Number: TRSS5-10

■TRSS (Stainless Steel)

Part Number		Unit Price	Volume Discount Rate		
Type	M - L	1 ~ 29 pc(s).	30 ~ 99 pcs.	100 ~ 149 pcs.	150 ~ 500 pcs.
TRSS	2 - 3				
	4				
	5				
	6				
	8				
	2.5 - 3				
	4				
	5				
	6				
	8				
	10				
	2.6 - 3				
	4				
	5				
	6				
	8				
	10				
	3 - 4				
	5				
	6				
	8				
	10				
	12				
	4 - 4				
	5				
	6				
	8				
	10				
	12				
	15				
	5 - 6				
	8				
	10				
	12				
	15				
	20				
	6 - 8				
	10				
	12				
	15				
	20				