Hex Socket Flat Head Cap Screws
Stainless Steel (Available in Box)



Type	Material
BOX-SFB	EN 1.4301 Equiv.



MxP (Coarse)	A Min.	A Max.	E (Max.)	B
3x0.5	5.54	6.72	1.86	2
4x0.7	7.53	8.96	2.48	2.5
5x0.8	9.43	11.2	3.1	3
6x1.0	11.34	13.44	3.72	4

Available as a single item and in package. P.188

Please specify in box quantity when ordering.
One box is shipped for an order of 1.

Ordering Example — Part Number: BOX-SFB5-10

■Box package is cost-saving for in-house stock or when large quantities are needed.

Part Number Type	Part Number M-L	Unit Price 1 to 10 boxes: Price per pkg.	Unit Price 1 to 10 boxes: 1 Box	Pcs./ Box
BOX-SFB (Stainless Steel)	3- 6			1,000 pcs./box
	8			
	10			
	12			
	15			
	4- 8			
	10			
	12			
	15			
	5-10			500 pcs./box
	12			
	15			
	20			
	6-10			
	12			
	15			
	20			
	25			300 pcs./box

Hex Socket Flat Head Cap Screws
Available in Stainless Steel (Available in Pkg./Single item)

■Hex Socket Flat Head Cap Screws - Stainless Steel



Type	Material	Surface Treatment	Strength Class
SFB PACK-SFB(Pkg.)	EN 1.4301 Equiv.	-	A2-50 Equiv.



MxP (Coarse)	A Min.	A Max.	E (Max.)	B (Nominal)
2x0.4	3.7	4.0	1.2	1.3
2.5x0.45	4.7	5.0	1.5	1.5
3x0.5	5.54	6.72	1.86	2.0
4x0.7	7.53	8.96	2.48	2.5
5x0.8	9.43	11.2	3.1	3.0
6x1.0	11.34	13.44	3.72	4.0
8x1.25	15.24	17.92	4.96	5.0
10x1.5	19.22	22.4	6.2	6.0

■SFB (Stainless Steel)

Part Number Type	Part Number M-L	ℓ	Unit Price 1 ~ 29 pcs.	Volume Discount Rate 30 ~ 49 pcs.	Volume Discount Rate 50 ~ 500 pcs.
SFB	3- 5	Studs - Fully Threaded			
	6				
	8				
	10				
	12				
	15				
	20				
	25				
	30				
	4- 8	Studs - Fully Threaded			
	10				
	12				
	15				
	20				
	25				
	30				
	5- 8	Studs - Fully Threaded			
	10				
	12				
	15				
	20				
	25				
	30				
	6-10	Studs - Fully Threaded			
	12				
	15				
	20				
	25				
	30				

■PACK-SFB (Pkg.)

Part Number Type	Part Number M-L	ℓ	Qty. / Pack	Unit Price 1 ~ 2 pkg(s).	Volume Discount Rate 3~10 pkgs.
PACK-SFB	2- 4	Studs - Fully Threaded	100 pcs./ pkg.		
	5				
	6				
	2.5- 5				
	6				
	8				
	3- 5				
	6				
	8				
	10				
	12				
	15				
	20				
	25				
	30				
	4- 6				
	8				
	10				
	12				
	15				
	20				
	25				
	30				
	5- 8				
	10				
	12				
	15				
	20				
	25				
	30				
	6-10				
	12				
	15				
	20				
	25				
	30				
	8-12		50 pcs./ pkg.		
	15				
	20				
	25				
	30				
	10-15		20 pcs./ pkg.		
	20				
	25				
	30				

When placing an order, please specify number of packages.

Ordering Example — Part Number:
FB6-10
SFB3-5
PACK-SFB2-6

* The strength class signifies the screw's tensile strength.

(Ex.) A2-50
- This indicates that the minimum value of tensile strength is 500N/mm².
- The steel class is A2 (Austenitic Stainless Steel)